

Water purifier SEAGULL IV ® X-2

Field of application

- Homes
- Boats
- Motorhomes and Caravans

Features

- pressure vessel in AISI 304 stainless steel
- easy replacement of the cartridge

Technical data

- | | |
|----------------------|--------------|
| ○ Cartridge | RS-2 SG |
| ○ Retention | 0,1 micron |
| ○ Flow | 8 Lt/min |
| ○ Capacity | 8.000Lt* |
| ○ Dimensions | Ø12,2xH25cm |
| ○ Operating pressure | da 1 a 8 ATM |

Phases of the purification process

1. Microfiltration through a structured matrix retention 0.1 micron con passaggio to remove water born pathogenic bacteria, parasites, radioactive particles and other micro particles.
2. Adsorption of organic chemical compounds by broad-spectrum absorbent substances particularly effective against chlorine, pesticides, herbicides and methylmercury
3. Bactericidal and not bacteriostatic action
4. permanent induction in the matrix of + and – electrostatic charges to remove even smaller particles

Equipment

- Faucet for model X-1/F

Item

- | | |
|---------|------------------------|
| 10.04/B | Seagull IV X-2B Base |
| 10.04/F | Seagull IV X-2F Faucet |

* Valore medio soggetto a variazioni in base al tipo di affluente