

# Water purifier SEAGULL IV® X-6

## Field of application

- Hotels
- Restaurants
- o Hospitals

### **Features**

- o pressure vesel in AISI 304 stainless steel
- o easy replacement of the cartridge
- o SPARK-L-PURE does not remove bacteria

### Technical data

Cartridge
Retention
Flow
Capacity
Dimensions
Operating pressure
RS-6SG
1 micron
25 Lt/min
25.000 Lt\*
Ø25,4xH44,5cm
da 1 a 8 ATM

0

## Phases of the purification process

- 1. Microfiltration through a structured matrix retention 0.1 micron con passaggio to remove water born pathogenic bacteria, parasites, radioactive particles and other micro particles.
- 2. Adsorption of organic chemical compounds by broad-spectrum absorbent substances particularly effective against chlorine, pesticides, herbicides and methylmercury
- 3. Bactericdal and not bacteriostatic action
- 4. permanent induction in the matrix of + and electrostatic charges to remove even smaller particles

#### Item

10.05 Seagull IV X-6

<sup>\*</sup> Valore medio soggetto a variazioni in base al tipo di affluente